


AVANT

Spine
MIS
Instrumentation

AVANT MIS Instrumentation Ordering Information



Implant Ordering Information



Titanium Percutaneous MIS Rods	Catalog n°
Ti Percutaneous MIS Rod Ø5.50 x 30mm	A5R-55FL-030
Ti Percutaneous MIS Rod Ø5.50 x 35mm	A5R-55FL-035
Ti Percutaneous MIS Rod Ø5.50 x 40mm	A5R-55FL-040
Ti Percutaneous MIS Rod Ø5.50 x 45mm	A5R-55FL-045
Ti Percutaneous MIS Rod Ø5.50 x 50mm	A5R-55FL-050
Ti Percutaneous MIS Rod Ø5.50 x 55mm	A5R-55FL-055
Ti Percutaneous MIS Rod Ø5.50 x 60mm	A5R-55FL-060
Ti Percutaneous MIS Rod Ø5.50 x 65mm	A5R-55FL-065
Ti Percutaneous MIS Rod Ø5.50 x 70mm	A5R-55FL-070
Ti Percutaneous MIS Rod Ø5.50 x 75mm	A5R-55FL-075
Ti Percutaneous MIS Rod Ø5.50 x 80mm	A5R-55FL-080
Ti Percutaneous MIS Rod Ø5.50 x 90mm	A5R-55FL-090
Ti Percutaneous MIS Rod Ø5.50 x 100mm	A5R-55FL-100
Ti Percutaneous MIS Rod Ø5.50 x 110mm	A5R-55FL-110
Ti Percutaneous MIS Rod Ø5.50 x 120mm	A5R-55FL-120
Ti Percutaneous MIS Rod Ø5.50 x 130mm	A5R-55FL-130
Ti Percutaneous MIS Rod Ø6.00 x 30mm	A5R-60FL-030
Ti Percutaneous MIS Rod Ø6.00 x 35mm	A5R-60FL-035
Ti Percutaneous MIS Rod Ø6.00 x 40mm	A5R-60FL-040
Ti Percutaneous MIS Rod Ø6.00 x 45mm	A5R-60FL-045
Ti Percutaneous MIS Rod Ø6.00 x 50mm	A5R-60FL-050
Ti Percutaneous MIS Rod Ø6.00 x 55mm	A5R-60FL-055
Ti Percutaneous MIS Rod Ø6.00 x 60mm	A5R-60FL-060
Ti Percutaneous MIS Rod Ø6.00 x 65mm	A5R-60FL-065
Ti Percutaneous MIS Rod Ø6.00 x 70mm	A5R-60FL-070
Ti Percutaneous MIS Rod Ø6.00 x 75mm	A5R-60FL-075
Ti Percutaneous MIS Rod Ø6.00 x 80mm	A5R-60FL-080
Ti Percutaneous MIS Rod Ø6.00 x 90mm	A5R-60FL-090
Ti Percutaneous MIS Rod Ø6.00 x 100mm	A5R-60FL-100
Ti Percutaneous MIS Rod Ø5.50 x 110mm	A5R-60FL-110
Ti Percutaneous MIS Rod Ø5.50 x 120mm	A5R-60FL-120
Ti Percutaneous MIS Rod Ø5.50 x 130mm	A5R-60FL-130

Additional rod lengths are available upon request.



Titanium Lordosed Rods	Catalog n°
Ti Lordosed Rod Ø5.50 x 30mm	A5R-55L-030
Ti Lordosed Rod Ø5.50 x 40mm	A5R-55L-040
Ti Lordosed Rod Ø5.50 x 45mm	A5R-55L-045
Ti Lordosed Rod Ø5.50 x 50mm	A5R-55L-050
Ti Lordosed Rod Ø5.50 x 60mm	A5R-55L-060
Ti Lordosed Rod Ø5.50 x 70mm	A5R-55L-070
Ti Lordosed Rod Ø5.50 x 80mm	A5R-55L-080
Ti Lordosed Rod Ø5.50 x 90mm	A5R-55L-090
Ti Lordosed Rod Ø5.50 x 100mm	A5R-55L-100
Ti Lordosed Rod Ø5.50 x 110mm	A5R-55L-110
Ti Lordosed Rod Ø5.50 x 120mm	A5R-55L-120
Ti Lordosed Rod Ø5.50 x 130mm	A5R-55L-130
Ti Lordosed Rod Ø5.50 x 200mm	A5R-55L-200



ASTRA Cannulated Polyaxial Screws, Extended Tab	Catalog n°
Ti MIS Poly Screw Ø4.50 x 30mm	A5P-4530E-C
Ti MIS Poly Screw Ø4.50 x 35mm	A5P-4535E-C
Ti MIS Poly Screw Ø4.50 x 40mm	A5P-4540E-C
Ti MIS Poly Screw Ø4.50 x 45mm	A5P-4545E-C
Ti MIS Poly Screw Ø5.50 x 35mm	A5P-5535E-C
Ti MIS Poly Screw Ø5.50 x 40mm	A5P-5540E-C
Ti MIS Poly Screw Ø5.50 x 45mm	A5P-5545E-C
Ti MIS Poly Screw Ø5.50 x 50mm	A5P-5550E-C
Ti MIS Poly Screw Ø5.50 x 55mm	A5P-5555E-C
Ti MIS Poly Screw Ø6.50 x 35mm	A5P-6535E-C
Ti MIS Poly Screw Ø6.50 x 40mm	A5P-6540E-C
Ti MIS Poly Screw Ø6.50 x 45mm	A5P-6545E-C
Ti MIS Poly Screw Ø6.50 x 50mm	A5P-6550E-C
Ti MIS Poly Screw Ø6.50 x 55mm	A5P-6555E-C
Ti MIS Poly Screw Ø7.50 x 35mm	A5P-7535E-C
Ti MIS Poly Screw Ø7.50 x 40mm	A5P-7540E-C
Ti MIS Poly Screw Ø7.50 x 45mm	A5P-7545E-C
Ti MIS Poly Screw Ø7.50 x 50mm	A5P-7550E-C
Ti MIS Poly Screw Ø7.50 x 55mm	A5P-7555E-C
Ti MIS Poly Screw Ø7.50 x 60mm	A5P-7560E-C
Ti MIS Poly Screw Ø8.50 x 35mm	A5P-8535E-C
Ti MIS Poly Screw Ø8.50 x 40mm	A5P-8540E-C
Ti MIS Poly Screw Ø8.50 x 45mm	A5P-8545E-C
Ti MIS Poly Screw Ø8.50 x 50mm	A5P-8550E-C
Ti MIS Poly Screw Ø8.50 x 55mm	A5P-8555E-C

Non-self tapping screws are available as special order.



Miscellaneous	Catalog n°
T-30 Set Screw	A5S-T30


Ti Lordosed Rod Ø6.00 x 30mm	A5R-60L-030
Ti Lordosed Rod Ø6.00 x 40mm	A5R-60L-040
Ti Lordosed Rod Ø6.00 x 45mm	A5R-60L-045
Ti Lordosed Rod Ø6.00 x 50mm	A5R-60L-050
Ti Lordosed Rod Ø6.00 x 60mm	A5R-60L-060
Ti Lordosed Rod Ø6.00 x 70mm	A5R-60L-070
Ti Lordosed Rod Ø6.00 x 80mm	A5R-60L-080
Ti Lordosed Rod Ø6.00 x 90mm	A5R-60L-090
Ti Lordosed Rod Ø6.00 x 100mm	A5R-60L-100
Ti Lordosed Rod Ø6.00 x 110mm	A5R-60L-110
Ti Lordosed Rod Ø6.00 x 120mm	A5R-60L-120
Ti Lordosed Rod Ø6.00 x 130mm	A5R-60L-130
Ti Lordosed Rod Ø6.00 x 200mm	A5R-60L-200

Straight rods are also available.


Instrument Ordering Information



AVANT RCDF Sleeve
6400-47C




Rod Holder
6100-10



Rod Introducer — Push-Button Release
6100-12

Rod Introducer — Push-Button Release and Backstop
6100-12



Rod Introducer — Locking Wheel
6100-12K

Rod Introducer — Locking Wheel and Backstop
6100-12KS



Compression Forceps
6100-42-H




Small Fulcrum
6100-42-F1520



K-wires, Stainless Steel
6100-WV2

K-wires, Nitinol
6100-WV3



Cannulated Tap, Ø4.5mm
6300-71-45

Cannulated Tap, Ø5.0mm
6300-71-50

Cannulated Tap, Ø5.5mm
6300-71-55

Cannulated Tap, Ø6.5mm
6300-71-65

Cannulated Tap, Ø7.5mm
6300-71-75

Cannulated Tap, Ø8.5mm
6300-71-85



Rod Pass Indicator (Optional)
6100-34



AVANT Polyaxial Screwdriver
6400-02



T22 Hexalobe Driver
6300-22-M



T30 Self Retaining Driver with Dedicated Handle
6000-30-3
T30 Self Retaining Driver
6400-30S



T30 Hexalobe Driver
6400-30-M



Side-Loading Counter Torque Handle
6400-98S



Extended Tab Remover
6400-98S



AVANT Caliper
6400-09



Dilator #1
6100-51
Dilator #2
6100-52
Insulating Dilator
6100-53




10.5 Nm Torque-Limiting Handle
6300-02



Ratcheting T-Handle
6000-03



Palm Ratcheting Handle
6000-03-P



French Rod Bender
6000-16-S



777 Oakmont Lane - Westmont, IL 60559, USA
TEL + 1 630 920 7300 - FAX + 1 630 920 7310
TF + 1 877 731 SPINE (+ 1 877 731 7746)
www.spinecraft.com